



Disposable Filter Series 一次性使用呼吸过滤器系列

Effectively filtering virus&bacteria/
Heat and Moisture Exchange and Insulation
高效过滤病毒、细菌/具有气体保温保湿功能

新邦医疗旗下品牌
HUAKUN 华坤

Disposable HMEFs 一次性使用呼吸过滤器(人工鼻)

- Multiple filters to satisfy various requirements
- Matched with relative consumables such as anesthesia masks and circuits
- Moistening, warming and filtering gas output from respiratory machine and input in patients
- High bacterial viral efficiency>99.99%, insulation and moisturizing
- 提供多种人工鼻可满足临床不同的需求
- 可以与麻醉面罩、气路等机相关耗材连接使用
- 是用采湿化、温湿化过滤机或呼吸机等仪器出来并输入病人呼吸的气体
- 产品具有高效的病毒和细菌过滤率(病毒、细菌过滤率大于99.99%)



Model 产品型号	A1(3000)	B1(3003)	B2(3006)	F1(3019)	F2(3134)
Luer port Luer 接口	✓	✓	✓	✓	✓
Filtration efficiency 过滤效率	>99.99%	>99.99%	>99.99%	>99.99%	>99.99%
Resistance 流速阻力(10L/min)(kPa)	0.03	0.2	0.2	0.09	0.09
Resistance 流速阻力(10L/min)(kPa)	0.2	0.5	0.4	0.19	0.2
Compressible volume(可压缩容积)(ml)	19	13.9	17.5	17.4	21.4
Weight 重量(g)	30.6	22.9	28.6	32.6	32.6
Minimum tidal volume 最小潮气量(ml)	100	75	50	100	100

Model 产品型号	F2(3136)	F4(3152)	F5(3055)	I1(3321)	G3(3308)
Luer port Luer 接口	✓	✓	✓	✓	✓
Filtration efficiency 过滤效率	>99.99%	>99.99%	>99.99%	>99.99%	>99.99%
Resistance 流速阻力(10L/min)(kPa)	0.03	0.18	0.19	0.05	0.05
Resistance 流速阻力(10L/min)(kPa)	0.2	0.85	0.5	0.11	0.11
Compressible volume(可压缩容积)(ml)	19.9	11.1	14.1	20	48.6
Weight 重量(g)	30.3	21.2	14.3	24.5	25.1
Minimum tidal volume 最小潮气量(ml)	100	75	50	75	100

Ningbo Huakun Company

HUAKUN

Ningbo Huakun Medical Equipment Co., Ltd.
地址：中国宁波市慈溪市逍林镇逍林工业区1号
邮编：315300 电话：+86-514-32073411
传真：+86-514-32073412
邮箱：huakun@huakun.com
官网：www.huakun.com
网址：www.chinahuakun.com