



Disposable Filter Series 一次性使用呼吸过滤器系列

Effectively filtering virus/bacteria/
Heat and Moisture Exchange and Insulation
高效过滤病毒、细菌/具有气体保温保湿功能

新医康 行业下品牌

HUAKUN 华坤

Disposable HMEFs 一次性使用呼吸过滤器(人工鼻)

- Multiple filters to satisfy various requirements
- Matched with relative consumables such as anesthesia masks and circuits
- Moistening, warming and filtering gas output from respiratory machine and input in patients
- High bacterial viral efficiency >99.99%, insulation and moisturizing
- 提供多种人工鼻可满足临床不同的需求
- 可以与麻醉面罩、管路等相关耗材连接使用
- 是用于雾化、温暖和过滤从呼吸机输出并输入病人呼吸的气体
- 产品具有高效的病毒和细菌过滤率(病毒、细菌过滤率≥99.99%)



Model 产品编码	A1(3000)	B1(3003)	B2(3006)	F1(3019)	F2(3144)
Luer port Luer 接口	√	√	√	√	√
Filtration efficiency 过滤效率	>99.99%	>99.99%	>99.99%	>99.99%	>99.99%
Resistance 流速阻力(l/sL/min)(kPa)	0.09	0.2	0.2	0.09	0.09
Resistance 流速阻力(l/sL/min)(kPa)	0.2	0.5	0.4	0.19	0.2
Compressible volume 可压缩容积(ml)	19	13.9	17.5	17.4	21.4
Weight 重量(g)	30.6	22.9	30.6	33.8	32.6
Minimum tidal volume 最小潮气量(ml)	100	75	50	100	100

Model 产品编码	F3(3136)	F4(3152)	F5(3055)	I1(3321)	G3(3308)
Luer port Luer 接口	√	√	√	√	√
Filtration efficiency 过滤效率	>99.99%	>99.99%	>99.99%	>99.99%	>99.99%
Resistance 流速阻力(l/sL/min)(kPa)	0.08	0.18	0.19	0.05	0.05
Resistance 流速阻力(l/sL/min)(kPa)	0.2	0.36	0.5	0.11	0.11
Compressible volume 可压缩容积(ml)	19.9	11.1	4.1	29	48.6
Weight 重量(g)	30.3	21.2	14.1	24.5	25.1
Minimum tidal volume 最小潮气量(ml)	100	75	50	75	100

Global Medical Company
HUAKUN

宁波华坤医疗器械有限公司
地址: 中国宁波市鄞州区中河街道七官桥村
电话: 0574-8330 3330
传真: 0574-8337 3411
邮编: 315000
邮箱: huakun@hkhgroup.com
网址: www.chinahuakun.com

Ningbo Huakun Medical Equipment Co., Ltd.
602-602 East Street, Chengzhou Town, Jiaxing Jiangsu, China
Tel.: 0574-8330 3330
Fax: 0574-8337 3411
P.C.: 315000
E-mail: huakun@hkhgroup.com
Web: www.chinahuakun.com